# **UP 10-16 Comfort PM, PM Auto**

The UP 10-16 pump is designed for recirculation of domestic hot water in single-family homes with dedicated hot-water return piping. Utilizing a low-noise permanent magnet motor, energy consumption is reduced to as little as 5 - 8.5 W. Selecting the Auto mode ensures that the pump runs only when required. The result is maximum comfort - no waiting for hot water plus decreased water and power consumption.



Fig. 9 UP 10-16 APM BU/LC

## **Applications**

- Domestic hot-water recirculation systems in singlefamily homes
- · small heating systems.

#### **Pumped liquids**

- · Domestic hot water
- · softened water
- · clean water.

The pump uses two temperature sensors, one within the pump and the other connected to the pump by a cable installed in the hot-water flow pipe. The pump is installed in the hot-water return pipe.




Fig. 10 UP 10-16 APM pump with built-in temperature sensor

### Three operating modes

#### 100 % mode

 Pump will operate 24/7/365 continuously at full speed.

## Temperature mode

 Pump will keep the water temperature within an automatically detected range.

#### Auto mode

 Pump will learn, store and adapt operating times to home hot water consumption patterns.

#### Disinfection feature

 Once per week, the pump will run a 15-minute disinfection cycle.

#### Vacation feature

If no tappings are detected in a 24-hour period, the pump will (self-modulate) automatically switch to standby mode (except for disinfection) and reactivate to the same consumptive pattern when 2 tappings occur within a 20-minute time period.

#### Motor

TM06 0034 4713

The motor is single-phase, 12-pole, permanent-magnet design, impedance-protected, double insulated, No additional motor protection is required.

Voltage	1 x 115/208-230 V, 50/60 Hz
Power	5 - 8.5 Watts
Enclosure class	IP42, type PM: IP44
Insulation class	F

# Maximum system pressure

145 psi (10 bar).

#### Ambient and liquid temperatures

The ambient temperature should always be lower than the liquid temperature, as otherwise condensation may form in the stator housing.

Liquid temperature: 36 °F (2 °C) to 185 °F (85 °C).

We recommend to keep the operating temperature as low as possible (e.g. 140  $^{\circ}$ F (60  $^{\circ}$ C)) to avoid calcium precipitation.

Description	Material
Stator housing	Aluminium
Spherical separator	Stainless steel
Rotor can, complete	Stainless steel/Tungsten carbide
Rotor, impeller	Stainless steel, EPDM, PPO, PFTE, graphite
Pump housing	EcoBrass
Isolating valve	EcoBrass
Screw	Stainless steel
Terminal box cover	PC/ABS
Motor cover	PPO
Power cable jacket	PVC
O-Rings	EPDM
Check valve	POM
Light	Lexan
Insulation cover	EPP 55
External sensor cable	PC/ABS


6

# Technical data

# 6. Technical data

# UP 10-16 Comfort PM, PM Auto

# UP 10-16 A/PM B5/BN5/BU



Flow range:  $0 - 2.2 \text{ gpm } (0 - 0.5 \text{ m}^3/\text{h})$ 

Head range: 0 - 3.9 ft (0 - 1.2 m)

Motors: Single-phase Max. liquid temperature: 185 °F (85 °C) Min. liquid temperature: 36 °F (2 °C)

Max. system pressure: 145 psi (10 bar)

Model	Volts	Amps	Watts	Нр	Capacitor
UP 10-16 B5/BN5/BU	115/208-230 V	0.23	5 - 8.5	-	-


# **Approvals**







Drinking Water System Components In Accordance with NSF/ANSI 372

#### UP 10-16 PM B5, BN5 APM B5, BN5





UP 10-16 APM BU



ПЭ	
	TM06 0684 0714

Model	Product number – 115/208-230 V	Dimensions [inches (mm)]						Shipping	
		L1	H1	H2	Н3	B1	B2	Connection	<ul><li>weight [lbs (kg)]</li></ul>
UP10-16 PM B5/LC	98420206	3.13 (79)	1.0 (25.4)	0.5 (12.7)	5.25 (133) 2	2.67 (68)	3.28 (83)	1/2" Sweat	2.9 (1.3)
UP10-16 PM BN5/LC	98420210	3.13 (79)		0.5 (12.7)				1/2" NPT	3.4 (1.5)
UP10-16 A PM B5/LC	98420222	3.13 (79)		0.5 (12.7)				1/2" Sweat	2.9 (1.3)
UP10-16 A PM BN5/LC	98420223	3.13 (79)		0.5 (12.7)				1/2" NPT	3.4 (1.5)
UP10-16 A PM BU/LC	98420224	4.33 (110)		0.88 (23)				1 1/4" NPSM	3.8 (1.7)

Note: Models have a 6 ft (1.8 m), 3-prong power cord. Maximum external sensor cable length 8 ft (2.4 m). UP 10-16 A PM BU/LC with integral check valve. Dimensions in inches unless otherwise noted.