



SERVICE PARTS LIST

BULLETIN NO.
54-00-3715

SPECIFY CATALOG NO. AND SERIAL NO. WHEN ORDERING PARTS				REVISED BULLETIN	DATE
M18™ Dual Slope Rotary LASER					July 2023
CATALOG NO.	3704-20	SERIAL NO.	M99A	WIRING INSTRUCTION	
	14-20-0432		N25A		

EXAMPLE:
Component Parts (Small #)
Are Included When Ordering
The Assembly (Large #).




FIG.	PART NO.	DESCRIPTION OF PART	NO. REQ.
1	05-74-0747	M4 x 10mm Pan Hd. Torx T-20 Screw	(4)
2	42-38-0044	Top Bumper w/PLB PT/ Rotary Laser	(1)
6	05-74-0748	M3 x 12mm PH Torx T-10 M Screw	(16)
7	31-44-0611	Rotary Handle A-Side	(1)
8	31-44-0612	Rotary Handle w/Vert. Feet /B-Side	(1)
10d	05-74-0758	M2.6 x 6mm T8 ST Screw with Slot	(2)
10e	-----	Coin Cell Cover	(1)
10f	42-70-0041	E-Clip / ID=1.9mm	(2)
20	42-38-0043	Top Bumper w/PLB PT Kit/Rotary laser	(1)
29	31-15-0226	Coin Cell Cover Assembly	(1)
60	22-38-0106	Rotary Detector Clamp Assembly	(1)
61	3714	Green Interior Rotary Laser Receiver	(1)
62	42-55-0129	BMC - Blow Molded Case	(1)
63	12-20-0451	Service Nameplate - Laser	(1)
64	10-22-0259	Warning Label - Laser	(1)
65	14-20-0432	Dual Slope Rotary Laser Remote Control	(1)
66	12-20-0403	Service Nameplate - Remote	(1)
67	12-20-0412	Service Nameplate - Receiver	(1)

FIG. NOTES
63, 64, 66, 67 A clean, dry surface is essential for proper performance for any adhesive system. The area intended for application of any adhesive label or nameplate must be prepared by cleaning with isopropyl and alcohol. The solvent is to be applied with a clean, lint free applicator the surface allowed to dry before applying the label or name plate.

Service needs pertaining to accuracy or calibration can only be performed at MILWAUKEE TOOL Central Repair:
1401 Sycamore Ave., Greenwood, MS 38930-7277 OR
2198 Southtech Drive, Greenwood, IN 46143-6725


OR Via e-Service at: www.milwaukeetool.com/e-service.

QUESTIONS: please call 1.800.SAWDUST OR
Return it to a MILWAUKEE FACTORY SERVICE CENTER
location, freight prepaid and insured. A copy of the proof
of purchase should be included with the return product.

SCREW TORQUE SPECIFICATIONS				
FIG.	PART NO.	WHERE USED	SEAT TORQUE	
			(kgf-cm)	(lb-in)
10d	05-74-0758	Coincell Cover	5.0 ± 0.5	4.3 ± 0.4

MILWAUKEE TOOL • www.milwaukeetool.com
13135 W. LISBON RD., BROOKFIELD, WI 53005
Drwg. 1

DUAL SLOPE ROTARY LASER - RECEIVER



EXAMPLE:
Component Parts (Small #)
Are Included When Ordering
The Assembly (Large #).




FIG.	PART NO.	DESCRIPTION OF PART	NO. REQ.
18	05-74-0756	M2.5 x 15mm Pan Head T8 Screw	(8)
22	31-21-0048	Power Cell Door Hinge	(1)
23	31-21-0049	Power Cell Door Pin	(1)
24	05-74-0754	M2 x 8mm Pan Head T6 ST Screw	(3)
30	05-74-0761	M3x5mm Pan Head H2 ST Screw	(1)
31	43-44-0613	Leak Test Gasket/ ID=3mm T=1.2mm	(1)
53	31-50-0201	Bottom Housing Assembly/Detector	(1)
54	31-21-0052	Power Cell Door Assembly/Detector	(1)
55	31-21-0051	Power Cell Door Kit/Detector	(1)
56	43-44-0612	Leak Test Gasket Kit	(1)
61	3714	Dual Slope Rotary Laser Receiver	(1)
67	12-20-0412	Service Nameplate	(1)

DUAL SLOPE ROTARY LASER - REMOTE CONTROL

FIG.	PART NO.	DESCRIPTION OF PART	NO. REQ.
9	05-74-0756	M2.5 x 15mm Pan Head T-8 Screw	(6)
12	31-21-0048	Power Cell Door Hinge	(1)
13	31-21-0049	Power Cell Door Pin	(1)
14	05-74-0754	M2 x 8mm Pan Head T-6 ST Screw	(3)
21	05-74-0761	M3x5mm Pan Head H2 ST Screw	(1)
22	43-44-0613	Leak Test Gasket/ ID=3mm T=1.2mm	(1)
43	31-50-0207	Bottom Housing Assembly /Remote	(1)
44	31-21-0053	Power Cell Door Kit /Remote	(1)
45	31-21-0054	Power Cell Door Assembly /Remote	(1)
46	43-44-0612	Leak Test Gasket Kit	(1)
66	12-20-0403	Service Nameplate	(1)

